


## Chapel / Transfer Trolley



- Small 1170 x 500 mm platform
- Bearing rollers
- Electric casket lock front and rear
- Durable PVC top surface
- Removable battery pack
- Linak electrics 24 volt system
- 200 diameter rubber tyres for smooth transfer
- Foot brake
- High/Low adjustable 480 - 880 mm operated via handset
- Zinc epoxy coated frame



### Warranty Information

- 5 Years

sova / dignity in motion

Code	Display Name	Total Length	Total Width	Total Height	Safe Working Load
FUN100610	Chapel Trolley - Extra Wide - Complete with Skirt	1200 mm	655 mm	500 - 900 mm	350 kg