

## DETA Flood Light - 24W LED - with Security Sensor



The Deta 24W LED Security Floodlight features a slim, durable, and modern aluminium IP65 rated housing and a beam angle of 100 degrees with an adjustable head to direct the 2400 lumens of light precisely. It comes with a 1-metre lead and plug for simple DIY installation or can be hardwired by an electrician.

- 2400 Lumens in daylight colour
- 1-metre Lead with plug
- IP65 Weather rated
- Quick install bracket and floor mount bracket included
- Hardwire option does not void warranty if installed by a licensed electrician

✔ Contracted DVA product



Code	Display Name	Total Length	Total Width	Total Height	Material	Unit Weight
GSP496217	DETA Flood Light - 24W LED - with Security Sensor	150 mm	50 mm	120 mm	Aluminium	1 kg