

## Aspire Evoke 2 Wheelchair



- The Evoke 2 is designed for the user who wants a lightweight, highly adjustable manual wheelchair
- The [Contoured Padded Overlay](#) (shown in image #2) is a stylish recommended accessory for the Aspire Evoke 2. The contoured padded overlay offers the user increased comfort and is ideal for those who are in their wheelchair for longer periods of time. The mild contouring assists in positioning and pressure distribution, while the fabric allows air movement, increasing breathability. It is easily removed to allow washing when required
- Swing-in / out, height adjustable and removable foot rests – this facilitates user transfers and allows optimal positioning for the changing needs of the user
- Strong, Nylon upholstery with a comfortable cushion and padded backrest. For increased comfort, a padded overlay is available as an accessory
- Depth adjustable seating with rear angle adjustability – for more accurate positioning, customisability and increased user comfort
- Quick release 24" solid rear tyres - the wheels are easily removed to reduce the weight of the chair for transport and storage.
- Crash Tested – to AS/NZ3616.196

**Prescribing Therapists:** Click here to download our [Clinical Assistance Guide](#)

### Warranty Information

- 2 Years Frame
- 1 Year Components

✔ Contracted DVA product

✔ Contract approved

### ndis

**Item Code:**

05\_122203104\_0105\_1\_2

**Wheelchair Manual –**

**Composite:**05\_417\_0105\_1\_2

Click [here](#) for more information

### Compliance

AS3696-1:2008

| Code      | Display Name  | RRP  | Box Quantity | Safe Working Load | Material  | Unit Weight | Colour | Seat Depth   | Seat Width | Seat To Floor Height | Seat To Footrest | Backrest Height |
|-----------|---|------|--------------|-------------------|-----------|-------------|--------|--------------|------------|----------------------|------------------|-----------------|
| MWS449500 | Aspire Evoke 2 - 350mm Wide                               | 1049 | 1            | 150 kg            | Aluminium | 14.8 kg     | Silver | 400 - 475 mm | 350 mm     | 440 - 480 mm         | 440 - 480 mm     | 430 - 490 mm    |
| MWS449510 | Aspire Evoke 2 - 400mm Wide                               | 1049 | 1            | 150 kg            | Aluminium | 14.9 kg     | Silver | 400 - 475 mm | 400 mm     | 440 - 480 mm         | 440 - 480 mm     | 430 - 490 mm    |
| MWS449520 | Aspire Evoke 2 - 450mm Wide                               | 1049 | 1            | 150 kg            | Aluminium | 15.0 kg     | Silver | 400 - 475 mm | 450 mm     | 440 - 480 mm         | 440 - 480 mm     | 430 - 490 mm    |
| MWS449530 | Aspire Evoke 2 - 500mm Wide                               | 1049 | 1            | 150 kg            | Aluminium | 15.1 kg     | Silver | 400 - 475 mm | 500 mm     | 440 - 480 mm         | 440 - 480 mm     | 430 - 490 mm    |
| WCA848592 | Attendant Brakes Kit without Wheels                       | 150  | 1            | -                 | -         | -           | -      | -            | -          | -                    | -                | -               |
| WCA848594 | Attendant Propelled Conversion Kit with Brakes and Wheels | 268  | 1            | 120 kg            | -         | -           | -      | -            | -          | -                    | -                | -               |